

PRODUCT DATASHEET PANEL 625 SURFACE MOUNT KIT H75

SURFACE MOUNT KIT | Reinforced surface mount frames for panel luminaires



Areas of application

- H75 versions suitable for all LEDVANCE Panels
- H50 versions suitable only for LEDVANCE Biolux Panel and Panel Protect

Product benefits

- Ready-to-mount thanks pre-assembled magnetic corners
- Crossbar for advanced stability
- H50 version with slim design fits for panels with an overall height of 38 mm (Panel + driver)

Product features


- Extruded aluminum frame
- Mount frames available in 75 mm (H75) or 50 mm (H50) height
- Available in white (like RAL9003) or black (like RAL9005) color



TECHNICAL DATA

Dimensions & Weight

| Length | 625.5 mm |
|----------------|-----------|
| Width | 625.5 mm |
| Height | 75.0 mm |
| Product weight | 1700.00 g |



PL 625 SURFACE MOUNT KIT H75

Materials & Colors

| Product color | White |
|--------------------------|----------|
| RAL Color (most similar) | RAL 9003 |

Application & Mounting

| Mounting type | Surface |
|--------------------------|---------|
| Mounting location | Ceiling |
| Replaceable light source | No |

DOWNLOAD DATA

| Tender texts | Document name |
|------------------|--|
| Tender documents | SURFACE MOUNT KIT 625 SURFACE MOUNT KIT H75-EN |

LOGISTICAL DATA

| Product code | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Gross weight | Volume |
|---------------|------------------------------|--------------------------------------|--------------|------------------------|
| 4058075472938 | Folding box 1 | 630 mm x 81 mm x 631 mm | 2138.00 g | 32.20 dm ³ |
| 4058075472945 | Shipping box 4 | 650 mm x 355 mm x 660 mm | 10045.00 g | 152.30 dm ³ |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.